RX12K, RX12KPS & RX12KIS

Surface Mount Lift Rack

SPECIFICATIONS





RX12KIS Shown


Site Specifications			
Power Requirements	208-230 VAC, single phase power, 26 Amp		
Air Supply Requirements	125-150 PSI (8.6-10.3 bar)		
Minimum Concrete Spec.	3 in. (76 mm) thick, 3000 PSI (20,700 kPA) rating		
Maximum Floor Slope	2 in. (51 mm) over 126 in. (3200 mm)		
Product Specifications			
Max Vehicle Weight	12,000 lbs. (5500 kg)		
Max Wheelbase			
General Service	184 in. (4673 mm)		
Two-Wheel Alignment	179 in. (4547 mm)		
Four-Wheel Alignment	158 in. (4013 mm)		
Alignment Height	All lock positions		
Min. Four-Wheel Alignment	88 in. (2235 mm)		
Lifting Speed	1 speed, 55 seconds		
Lowering Speed	2 speed, 25 seconds		

MODEL FEATURES / DIMENSIONS / OPTIONS

Feature	K	KPS	KIS
6000-lb Swing Air Jacks (2)	Ø	Ø	Ø
Two-Speed Lowering	Ø	Ø	Ø
Fully Integrated Alignment		Ø	Ø
POWER SLIDE		Ø	Ø
INFLATION STATION			Ø

Dimension				
Length (L)	266 in. (6766 mm)			
Elevated Length (L2)	234 in. (5943 mm)			
Outside Width (W1)	88.5 in. (2248 mm)			
Inside Width (W2)	40 in. (1016 mm)			
Runway Width (R)	24 in. (610 mm)			
Raised Height (H1)	71 in. (1803 mm)			
Stack Height (H2)	10 in. (254 mm)			

Options	Add Length	Kit #
Approach Ramp Extensions (Back)	5 in. 127 mm	20-3113-1
Approach Ramp Extensions (Back)	27 in. 686 mm	20-2169-1
Approach Ramp Extensions (Back)	37 in. 940 mm	20-2189-1
Conventional Sensor Extensions (Front)	12 in. 305 mm	20-2497-1
Drive-Thru Kit (Front)	53 in. 1346 mm	20-2498-1
Extended Drive-Thru Kit (Front)	61 in. 1549 mm	20-2501-1



For lift rack information visit: www.hunter.com/lift-racks

For general inquiries visit: www.hunter.com or call 800-448-6848 For local contact visit: www.hunter.com/contact-hunter


Continued on Page 2

RX12K, RX12KPS & RX12KIS

Surface Mount Lift Rack

HUNTEREngineering Company

SPECIFICATIONS



Positioning of control console is limited to a maximum space between console and rack of 6 feet (1829 mm) at the approach ramp end and 16 1/2 feet (5029 mm) at the turnplate end. Additional threshold will be required (refer to Installation Instruction for details).